

# INSTALLATION INSTRUCTIONS

## Scensibles® SecureFit360® High Density Poly Liner Bags



Made with a strap that wraps around bottom of receptacle to secure in place and contain waste for safe removal.

### View Instructional Videos:



### ITEM# LBSF500HD

**Universal liner for use on all makes and models of surface or wall mount plastic, metal, and stainless steel receptacles, including:** Hospeco Brands Group (EVNT-CWR, CDSS, CDWM, ND-IE, ND-1W, 250-201), Bobrick, Bradley, ASI and Impact  
**Size:** 12.5" x 23" with 7.5" strap  
**Case Pack:** 500/case

#### ■ STEP 1

Insert the body of the bag into the receptacle with strap hanging in front.



#### ■ STEP 2

Open bag slightly, then fold back over front and sides of receptacle. Close lid.



#### ■ STEP 3

Pull gently on hanging strap to fit around bottom of receptacle. Open lid to adjust bag as needed to ensure proper fit.



#### ■ STEP 4

To remove, pull up on strap around the bottom to discard contents.

