



scensibles®

Hygienic Disposal System For Menstrual Care Products



SCENSIBLES® PERSONAL DISPOSAL BAGS

- Single-use bag for sanitary pads, tampons, panty liners and wipes
- Contemporary pattern masks the contents
- Easy 4" handle-tie closures help completely conceal contents
- Pleasant fresh fragrance
- Built-in antimicrobial agents inhibit the growth of odor-causing bacteria on the bag
- Interleave folded in refill box for easy dispensing
- 1 mil high density poly with 20% pre-consumer recycled material
- Box Size: 3.5" x 5" x .5"
- Bag Size: 3.375" x 9.75" x 2" gusset

Additional **Scensibles® Bag Dispensers** recommended for placement in each stall.



| Item # | Description | Selling Unit | Case Pack |
|--|---|--------------|----------------------|
| SBX50 | Personal Disposal Bags, Refill Pack, Pink, 1 mil HDPE | 1 cs | 50 bgs/bx - 24 bx/cs |
| Fits compact dispensers SDW, SDSC, SDBL, SDSS Fits combination dispenser receptacles EVNT-CWR, CDW, CDWM, CDSS | | | |
| SDW | Scensibles® Compact Dispenser, White Plastic | 1 ea | 12/cs |

SCENSIBLES® UNIVERSAL POLY LINER BAGS

- Completely covers inside surface to conceal waste and reduce contamination
- .47 mil high density polyethylene
- Fresh fragrance and built in antimicrobial for odor-control
- Snug fit prevents bag from collapsing in receptacle
- Clear to allow cleaning staff to see and avoid needles and other sharps



The **SecureFit360® wraparound strap** secures liner in place and provides for safe removal by maintenance staff.

| Item # | Description | Selling Unit | Case Pack |
|--|--|--------------|-----------|
| LBS500HD | Small - 9.5" x 3.5" x 12", Frosted Clear, HDPE | 1 cs | 500/cs |
| Fits CDW, CDB, HS-6140WP | | | |
| LBM500HD | Medium - 10" x 4" x 12", Frosted Clear, HDPE | 1 cs | 500/cs |
| Fits CDW, CDB, CDSS, CDWM, HS-6140WP, 250-201W, ND-1E, ND-1W and recessed and dual-access receptacles with removable molded liners | | | |
| LBSF500HD | SecureFit360® - 12.5" x 23", 7.5" strap, Frosted Clear, HDPE | 1 cs | 500/cs |
| Fits EVNT-CWR, CDSS, CDWM, 250-201W, ND-1E, ND-1W and most common surface or wall mount receptacles | | | |

CONTACT YOUR LOCAL REPRESENTATIVE OR CALL 800-942-9199 FOR MORE INFORMATION.
WWW.HOSPECOBRANDS.COM

INSTALLATION INSTRUCTIONS

Scensibles® SecureFit360® High Density Poly Liner Bags

scensibles®

View an Instructional
Video at:



Made with a strap that wraps around bottom of receptacle to secure in place and contain waste for safe removal.

ITEM# LBSF500HD

Universal liner for use on all makes and models of surface or wall mount plastic, metal, and stainless steel receptacles, including: Hospeco Brands Group (EVNT-CWR, CDSS, CDWM, ND-1E, ND-1W, 250-201W), Bobrick, Bradley, ASI and Impact

Size: 12.5" x 23" with 7.5" strap

Case Pack: 500/case



■ STEP 1

Insert the body of the bag into the receptacle with strap hanging in front.



■ STEP 2

Open bag slightly, then fold back over front and sides of receptacle. Close lid.



■ STEP 3

Pull gently on hanging strap to fit around bottom of receptacle. Open lid to adjust bag as needed to ensure proper fit.



■ STEP 4

To remove, pull up on strap around the bottom to discard contents.



CONTACT YOUR LOCAL REPRESENTATIVE OR CALL 800-942-9199 FOR MORE INFORMATION.
WWW.HOSPECOBRANDS.COM